


## Single-Use Standard Bags

Bags and Accessories for a Variety of Applications



B. Braun's OEM Division offers a varied selection of single-use standard bags for solutions as part of its complete medical device contracting manufacturing capabilities. The bags are manufactured at a B. Braun FDA-registered foreign production site, which has state-of-the-art technologies and adheres to international quality standards.

## Material:

- Clear or Yellow EVA
- Single-layer or Multi-layer

Multi-layer bags provide barrier properties against oxygen penetration and UV radiation for stability.

## **Configurations:**

- 50-4,000 ml
- Single or Dual Chamber
- Port options according to filling type
- Custom printing available

Two-chamber design allows aseptic filling and separate storage of other constituents. Our single use standard bags can be incorporated into a complete medical device. B. Braun also offers on-site engineering assistance, packaging, sterilization and other services for a reliable outsourced solution.

## Port Options

Filling	Available with complimentary caps
Female Lock Connector	
Male Lock Connector for filling ports	
Female Luer Lock Connector for syringe filling	444
Administration	For use with IV administration sets
Twist-Off Connector	
Vial Adapter	
Tear-Off Connector	
Membrane Connector	
	Front detectable and an
Injection	For injection or withdrawal of fluids
Injection White Injection Port	
White Injection Port	
White Injection Port  Blue Injection Port  Non-Reusable Injection Site	
White Injection Port  Blue Injection Port  Non-Reusable Injection Site with cap	For use with ports
White Injection Port  Blue Injection Port  Non-Reusable Injection Site with cap  Protection  Male Lock Cap with filter for	For use with ports
White Injection Port  Blue Injection Port  Non-Reusable Injection Site with cap  Protection  Male Lock Cap with filter for filling ports	For use with ports
White Injection Port  Blue Injection Port  Non-Reusable Injection Site with cap  Protection  Male Lock Cap with filter for filling ports  Vented Cap for filling ports  Female Lock Cap for filling	For use with ports







